



KINTEK SOLUTION

Handheld Xrf Analyzers Catalog

Contact us for more catalogs of Sample Preparation, Thermal Equipment, Lab Consumables & Materials, Bio-Chem Equipment, etc.

KINTEK SOLUTION

COMPANY PROFILE

>>> About Us

Company Profile

Kintek Solution Ltd is one technology orientated organization, team members are devoted to probing the most efficient and reliable technology and innovations in the scientific researching equipment, fields like biochemical reacting, new materials researching, heat treatment, vacuum creating, refrigerating, as well as pharmaceutical and petroleum extracting equipment.

Products & Services

Kintek Solution Ltd is headquartered in Zhengzhou, the capital city of Henan Province, China, and its core business includes the manufacture, distribution and sale of all types of scientific research equipment and laboratory consumables. The wide range of products and services covers the following main areas:

- **Sample Preparation Equipment:** We provide high-performance sample preparation equipment such as tablet presses, ball mills, vibrating sieves and tablet punching machines, which are capable of meeting a wide range of sample preparation needs and ensuring high quality experimental data and research results.
- **Thermal Equipment:** Our thermal equipment includes tube furnaces, sintering furnaces, vacuum furnaces, atmosphere furnaces, graphite furnaces, dental furnaces, rotary furnaces, and high-temperature furnaces (e.g., MPCVD, CVD, PECVD, electric rotary kilns). These facilities excel in high-temperature processing and materials synthesis, meeting a wide range of needs from basic research to industrial production.
- **Biochemical equipment:** We offer a wide range of biochemical laboratory equipment, including rotary evaporators, vacuum pumps, cold trap chillers,

heating circulators, reactors, short-range distillation equipment, sterilization equipment, and homogenizers. These equipments are widely used in the fields of chemical reaction, biological processing and pharmaceutical manufacturing.

- **Laboratory Consumables:** We supply a wide range of laboratory consumables such as fine ceramic products, electrochemical consumables, PTFE material products, high purity materials, battery materials, chemical vapor deposition materials, optical materials, thin film deposition components and glass materials. These consumables provide the necessary support for laboratories to ensure the smooth running of experimental processes.

Technological Advantages

Kintek Solution Ltd has significant technological strengths in the field of scientific research equipment and technical solutions, which enable us to stand out in a competitive marketplace and support our customers with cutting-edge technology. The following are our key technological strengths:

Advanced R&D capabilities

- **Technological Innovation:** Our R&D team is committed to exploring and developing the latest technologies to keep our equipment at the forefront of the industry through continuous technological innovation.
- **Customized solutions:** Based on the specific needs of our customers, we are able to develop and provide customized equipment to meet specific research requirements and application scenarios.
- **Cooperative R&D:** We cooperate with leading research institutes and higher education institutions around the world to carry out R&D projects on cutting-edge technologies to ensure that our technologies are always at the forefront of the industry.

High-performance equipment

- **Precision design:** Our equipment adopts advanced design concepts to ensure high precision, reliability and performance to meet the stringent requirements of scientific research and industrial applications.
- **Advanced materials:** We use high-quality materials and components to improve the durability and stability of our equipment, extend its service life and reduce maintenance costs.

Strict quality control

- Standardized production: All equipment is manufactured in accordance with international quality standards, and each production step is strictly controlled to ensure product consistency and reliability.
- Comprehensive testing: Comprehensive performance testing and quality inspection are carried out before the equipment is delivered to ensure that it meets the customer's technical specifications and operational requirements.

Comprehensive technical support

- Technical Service: Provide comprehensive technical support and after-sales service, including equipment installation, commissioning, training and maintenance, to ensure that customers can use our products efficiently.
- Rapid Response: We have established a rapid response mechanism, which can promptly solve the problems encountered by customers in the process of use and reduce equipment downtime.

Innovative technology integration

- System Integration: We integrate advanced control systems and automation technologies into our equipment to improve operational efficiency and data accuracy, and streamline operational processes.

Through these technological advantages, Kintek Solution Ltd is able to continue to provide our customers with innovative, efficient and reliable scientific research equipment and solutions to promote the continuous progress of scientific research and industrial applications.

Market position and customers

Kintek Solution Ltd is positioned in the market as a leading global provider of high-tech research equipment and solutions, specializing in biochemical reactions, new materials research, heat treatment, vacuum manufacturing, refrigeration, as well as pharmaceuticals and oil extraction. We are committed to brand leadership in research equipment by providing innovative technology and high quality equipment to meet the needs of research organizations and industrial companies in complex research and production processes.

Core Market Positioning:

- **Specialization:** We focus on high technology and scientific research, providing advanced equipment and solutions for specialized research institutes, laboratories and industrial applications.
- **High-end customers:** Our main customers include world-renowned universities, research institutes and various industrial enterprises, which usually have high requirements for equipment performance and technology.
- **Technological Innovation:** We are committed to technological innovation and customized solutions to ensure that our customers receive cutting-edge technical support to meet the ever-changing needs and challenges in the market.

Market Customer Groups:

- **Research Institutes and Universities:** including the world's leading research institutes and institutions of higher learning, who require high-performance research equipment and technical support for basic research, applied research and technology development.
- **Industrial companies:** covering a wide range of industries such as pharmaceuticals, oil extraction, new materials manufacturing and electronic materials production, these companies rely on reliable equipment and solutions to ensure product quality and productivity during production.
- **Laboratories and test centers:** organizations that provide laboratory services and quality testing, requiring accurate laboratory equipment and instruments for sample analysis and testing.
- **Technology Development Companies:** Companies that specialize in the development and application of new technologies and have a high demand for innovative equipment and technical solutions to support their R&D projects and technology validation.

Through clear market positioning and customer groups, we are committed to promoting scientific and technological progress, supporting the innovation and development of our global customers, and continuing to provide high-quality products and services to the market.

Team Introduction

The team at Kintek Solution Ltd is at the heart of the company's success. In order to realize our vision and maintain our leadership position in the field of high-tech research equipment, we are committed to building an exceptional team with the following attributes:

1. Professionalism

- **Technical Expertise:** Our team consists of technical experts and engineers in the field with deep expertise and technical backgrounds to meet complex technical challenges and innovation needs.
- **Industry experience:** We bring together professionals with extensive experience in the fields of research equipment, material science and engineering technology to ensure a precise grasp of market needs and technological trends.

2. Innovative Spirit

- **R&D-driven:** The team encourages innovative thinking and technological exploration, supports employees to participate in R&D projects on cutting-edge technologies, and continuously pushes forward the technological advancement of products and solutions.
- **Flexible Adaptation:** In the face of changing market environment, we have the ability to adapt quickly and flexibly to meet the changing needs of our customers.

3. Collaboration and Communication

- **Cross-sectoral collaboration:** The team maintains close collaboration between various departments, including R&D, production, sales and customer service, to ensure the smooth progress of projects and timely response to customer needs.
- **Efficient Communication:** Emphasize internal communication and information sharing, through efficient communication mechanisms and tools to ensure that all team members are consistent with the project goals and progress.

4. Customer Orientation

- **Customer Service:** Team members are customer-focused and committed to providing quality service and support to ensure that our customers have the best experience in using our products and solutions.

- Customized solutions: the ability to deeply understand the specific needs of customers and provide customized solutions to meet the special requirements of different customers.

5. Professional Training and Development

- Continuous Learning: We provide continuous training and learning opportunities for our team members to ensure that they are always up-to-date with the latest technology and industry knowledge.
- Career Development: We value the career development and growth of our employees, provide clear career paths and promotion opportunities, and motivate our employees to realize their personal goals and career aspirations within the company.

6. Corporate Culture

- Integrity and Responsibility: The team upholds integrity and responsibility, treats work and customers with honesty and fairness, and builds trust and long-term cooperative relationships.
- Unity and Collaboration: Focusing on the spirit of teamwork, the team emphasizes mutual support and joint efforts to achieve the company's goals and promote the overall success of the team.

By building such a highly qualified, innovation-driven and customer-oriented team, we ensure that Kintek Solution Ltd continues to lead in the field of scientific research equipment and provide excellent products and services to our customers worldwide.

At KINTEK, technology fuels our corporate spirit. This dynamic energy awaits you upon joining our team. Expect a distinctive cultural environment where our global business focus opens doors to diverse customs and traditions worldwide. Here, challenging roles promise to propel your career to new heights.

Our exceptional corporate culture sparks innovation, fosters care, and drives continuous progress among individuals and teams. Our team embodies youthfulness, positivity, enthusiasm, and a bold attitude toward challenges. Passionate about our business, our employees ardently contribute to the company's growth.

We seek individuals brave enough to embrace challenges, harbor grand ambitions, and thirst for knowledge. If you're driven by dreams and passion, and aspire to start your

entrepreneurial journey, KINTEK is the platform to actualize your career plans. We don't just offer opportunities; we pave the way for your future.

Join us at KINTEK, where innovation meets opportunity. Let's create a future that's as promising as your aspirations.

Future Plans

Kintek Solution Ltd's future plans are aimed at further strengthening our leadership position in the research equipment sector and driving the company forward in terms of technological innovation, market expansion and customer service. The following are our key future directions:

1. Technology Innovation and R&D

- Cutting-edge technology development: Continue to invest resources in the research and development of cutting-edge technologies, such as artificial intelligence, the Internet of Things and nanotechnology, in order to promote equipment intelligence and automation.
- New Product Lines: Expand existing product lines and develop equipment to meet emerging market needs, especially in the areas of biochemistry, biomedicine and high-performance materials.
- Cooperative R&D: Strengthen cooperation with international research institutes and institutions of higher learning to carry out joint R&D projects to ensure that the technology remains at the global leading level.

2. Market Expansion

- Global Market Expansion: Further expand the global market, especially in emerging markets and developing regions, establish more sales and service networks, and enhance the brand's international influence.
- Industry application: Explore and expand the application fields in other industries, such as new energy, environmental protection technology and intelligent manufacturing, to open up new business growth points.

3. Customer Service Enhancement

- Enhancement of customer support: Establish a more complete customer support system, provide 24/7 technical support and maintenance services, and ensure

the efficient experience of customers in the use of equipment.

- Customized services: Provide more customized services and solutions according to customers' individual needs to enhance customer satisfaction and loyalty.

4. Sustainable Development

- Environmentally friendly technology: Develop and adopt environmentally friendly materials and processes to reduce the environmental impact during the production and use of equipment and promote sustainable development.
- Energy saving and consumption reduction: Optimize the energy efficiency of equipment, reduce energy consumption, improve resource utilization efficiency, and support the development of green technology.

5. Internal optimization

- Intelligent management: Implement intelligent management systems and data analysis tools to improve productivity and management and reduce operating costs.
- Employee Training: Enhance employee training and skills upgrading to build a high-quality team to meet changing market demands and technological challenges.

6. Innovation ecosystem

- Establishment of innovation platform: Create innovation platforms and laboratories to support employees and partners in technological innovation and product development.
- Industry Chain Cooperation: Deepen cooperation with the upstream and downstream of the industry chain, integrate resources, and promote the development and implementation of industry technical standards and market norms.

Through these future plans, Kintek Solution Ltd will continue to lead the forefront of science and technology, provide customers with more advanced and reliable products and services, and at the same time, promote the sustainable development of the enterprise and the progress of the industry.



Handheld Alloy Analyzer

Item Number: XRF-900



Introduction

XRF900 are good choice for metal analysis in many fields, delivering rapid, accurate results right in your hand.

[Learn More](#)

Model	XRF-900	XRF-900P	XRF-900S
Excitation	Ceramic packaged microfocus X-ray tube, Ag Anode 50kV		
Detector	High performance Si-Pin detector	Optimized SDD detector (with Graphene window)	Optimized SDD detector(with Graphene window)
Resolution	140eV FWHM	129eV FWHM	129eV FWHM
Filter	Multi position automatic filter changer		
Window	Kapton with anti-puncture window design optional		
Battery	7.2V Li-ion battery,6800mAh		
Display	Capacitive touch screen (5 inch 720P)		
CPU	i.MX 8M Mini quad core 1.8GHz		
Signal Processor	4096-pixel multi-channel detector/80 MHz ADC digital signal processor		
Data Storage	Over 100,000 data storage		
Data transfer	WiFi/USB		
Structure design	Unique AXRUNI structure design, effectively increase the heat dissipation of the X ray tube		
Radiation safety	Safety Guard induction device, when there is no sample in the test area, the source will shut, providing maximum safety protection. Password-protected user security		
Camera(optional)	Integrated CCD camera with autofocus lens for positioning and recording measuring point positions		
Elements	Sb[Sn[Ag[Pd[Al[Mo[Nb[Zr[Bi[Pb[Se[W[Zn[Cu[Re[Ta[Hf[Sb[Sn[Ag[Pd[Al[Mo[Nb[Zr[Bi[Pb[Se[W[Zn[Cu[Re[Ta[Hf[Sb[Sn[Ag[Pd[Al[Mo[Nb[Zr[Bi[Pb[Se[W[Zn[Cu[Re[Ta[Hf[
Environment	Temp:-10°C~50°C Humidity 0%~80%		
Weight	Approx. 1.5kg (3.31bs) including battery		
Dimensions	LxWxH: 220mm*91mm*276mm		
Optional	With the innovatively designed AXRSMART mobile application, data can be viewed, shared, and printed in real time, and functions such as sample photo, GPS positioning, scanning, and data archiving can be supported. Optional data cloud service function support uploading the test results to a secure and encrypted cloud server, and perform statistics, query and analysis of large-scale analysis data.		
Special Accessories	In addition to conventional accessories, optional: welding mask, hot surface adapter. It can detect high temperature surfaces and vibrating surfaces without contact.		

Handheld Coating Thickness

Item Number: XRF-980



Introduction

The handheld XRF coating thickness analyzer adopts high-resolution Si-PIN (or SDD silicon drift detector) achieve an excellent measurement accuracy and stability. Whether it is for the quality control of coating thickness in the production process, or random quality check and complete inspection for incoming material inspection, XRF-980 can meet your inspection needs.

[Learn More](#)

Detector	High performance Si-Pin detector /Optimized SDD detector
Filter	Multi position automatic filter changer
Window	Kapton with anti-puncture window design optional
Collimator	5mm collimator
Battery	7.2V Li-ion battery 6800mAh
Display	Capacitive touch color display
Data storage	100000+data storage
Data transfer	WiFi USB
Radiation safety	Safety guard device, tube shutoff while no sample , Password-protected user security
Camera (optional)	Integrated CCD camera with autofocus lens for positioning and recording measuring point positions
Thickness	Generally within 50um (depending on material) Repeatability up to 0.1%
Environment Temp	-10°C~50°C Humidity 0%~80%
Weight	Approx. 1.5kg (3.3lbs) including battery
Dimensions	Lx WxH: 220mm*91mm*276mm
Software language	English and other languages

Handheld Precious Metal Analyzer

Item Number: XRF-990



Introduction

XRF990 handheld precious metal analyzer, based on advanced ceramic packaged microfocus X-ray tube and high-performance semiconductor detector, combined with advanced software algorithm, can quickly, accurately and non-destructively test gold, silver, platinum and other precious metals concentration in jewelry, to fast indentify the purity of jewelry, investment gold and various precious metal materials.

[Learn More](#)

Detector	High performance Si-Pin detector /Optimized SDD detector
Filter	Multi position automatic filter changer
Window	Kapton with anti-puncture window design optional
Collimator	5mm collimator
Battery	7.2V Li-ion battery,6800mAh
Display	Capacitive touch color display
Data storage	100000+ data storage
Data transfer	WiFi USB
Radiation safety	Safety guard device, tube shutoff while no sample , Password-protected user security
Camera (optional)	Integrated CCD camera with autofocus lens for positioning and recording measuring point positions
Elements	Au,Ag,Pt,Pd,Rh,Ru,Ir,Zn,Cu,Ni,Co,Fe and more can be added if required
Environment Temp	-10°C~50°C Humidity 0%~80%
Weight	Approx. 1.5kg (3.3lbs) including battery
Dimensions	LxWxH:220mm*91mm*276mm
Software language	English and other languages

Handheld Lithium Battery Analyzer

Item Number: XRF-970



Introduction

XRF970 handheld lithium battery analyzer, based on advanced ceramic packaged microfocus X-ray tube and high-performance semiconductor detector, combined with advanced software algorithms, can quickly and accurately analyze Ni, Co, Mn and other regulated elements in lithium batteries. It is an ideal portable analyzer for lithium battery manufacturers' process quality control and safety precautions, and for waste lithium battery recyclers' sorting tasks.

[Learn More](#)

Detector	High performance Si-Pin detector /Optimized SDD detector
Filter	Multi position automatic filter changer
Window	Kapton with anti-puncture window design optional
Collimator	5mm collimator
Battery	7.2V Li-ion battery 6800mAh
Display	Capacitive touch color display
Data storage	100000+ data storage
Data transfer	WiFi USB
Radiation safety	Safety guard device, tube shutoff while no sample , Password-protected user security
Camera (optional)	Integrated CCD camera with autofocus lens for positioning and recording measuring point positions
Elements	Ti V Cr Mn Fe Co Ni Hf Ta Re Cu Zn W Se Pb Bi Zr Nb Mo Al Pd Ag Sn Sb etc. and be customized
Environment Temp	-10°C~50°C Humidity 0%~80%
Weight	Approx. 1.5kg (3.3lbs) including battery
Dimensions	LxWxH: 220mm*91mm*276mm
Software language	English and other languages

Handheld Soil Analyzer

Item Number: XRF-600



Introduction

XRF600 Handheld Soil Analyzer is an important tool for soil and sediment screening. It can detect hazardous heavy metals within seconds. Using XRF600 for on-site rapid soil screening significantly reduces the number of samples that need to send to laboratory for analysis, reducing analysis costs and analysis time. And soil treatment and remediation costs can be minimized by rapidly screening and delineating contaminated areas and identifying remediation areas on-site.

[Learn More](#)

Model	XRF600/XRF600P/XRF600S
Excitation	High performance Ag target tube,50kV
Detector	High performance Si-Pin detector /Optimized SDD detector
Filter	Multi position automatic filter changer
Window	Kapton with anti-puncture window design optional
Collimator	5mm collimator
Battery	7.2V Li-ion battery,6800mAh
Display	Capacitive touch color display
Data storage	100000+data storage
Data transfer	WiFi/USB
Radiation safety	Safety guard device, tube shutoff while no sample , Password-protected user security
Camera (optional)	Integrated CCD camera with autofocus lens for positioning and recording measuring point positions
Elements	Ti[V]Cr[Mn]Fe[Co][Ni][Hf][Ta][Re][Cu][Zn][W][Se][Pb][Bi][Zr][Nb][Mo][Al][Pd][Ag][Sn][Sb] etc. and be customized
Environment Temp	-10°C~50°C Humidity 0%~80%
Weight	Approx. 1.5kg (3.3lbs) including battery
Dimensions	LxWxH:220mm*91mm*276mm
Software language	English and other languages

Handheld Mining Analyzer

Item Number: XRF-600M



Introduction

XRF600M, a fast, accurate, and easy-to-use handheld XRF mining analyzer designed for different analytical applications in the mining industry. The XRF600M provides on-site analysis of ore samples with minimal sample preparation, reducing the time for lab assay from days to minutes. With the fundamental parameters method, the XRF60M is capable of analyzing an ore sample without the need for any calibration standards.

[Learn More](#)

Model	XRF-600M/XRF-600MP/XRF-600MS
Excitation	Ceramic packaged microfocus X-ray tube, Ag target tube,50kV
Detector	High performance Si-Pin detector /Optimized SDD detector
Filter	Multi position automatic filter changer
Window	Kapton with anti-puncture window design optional
Collimator	5mm collimator
Battery	7.2V Li-ion battery,6800mAh
Display	Capacitive touch color display
Exceeding Alert	When elements concentration exceeds the setting limits, software will alert
One Touch Operation	One touch testing
Soil Moisture Correction	Analysis can automatically correct according to the soil moisture
Data storage	100000+data storage
Data transfer	WiFi□USB
Radiation safety	Safety guard device, tube shutoff while no sample ,Password-protected user security
Camera (optional)	Integrated CCD camera with autofocus lens for positioning and recording measuring point positions
Environment Temp	-10°C~50°C Humidity 0%~80%
Weight	Approx.1.5kg (3.3lbs) including battery
Dimensions	Lx WxH:220mm*91mm*276mm
Software language	English and other languages

In-Line Xrf Analyzer

Item Number: XRF-700



Introduction


AXR Scientific In-line XRF analyzer Terra 700 series can be flexibly configured, and can be effectively integrated with robotic arms and automatic devices according to the layout and actual situation of the factory production line to form an efficient detection solution that meets the characteristics of different samples. The whole process of detection is controlled by automation without too much human intervention. The entire online inspection solution can perform real-time inspection and quality control of production line products around the clock.

[Learn More](#)

Excitation Source	X-ray tube:Rhodium or tungsten anode target (optimized for application), 5 to 200 μ A, 8 to 50keV (4 W max)
Detector	High performance SDD detector
Power Supply	9 VAC power adapter
Analysis Mode	Alloy or Coating
Analysis range	Elements from Potassium (K19) to Uranium (U92)
IP Rating	IP54
Temperature Range	10C to 50C. continuous operation
Humidity	10 % to 90 % relative humidity, non-condensing
Operating System	Linux
Software	Proprietary data acquisition and processing software package

Xrf Spectrometer Module

Item Number: XRF-400



Introduction

Scientific In-line XRF Spectrometer Module series can be flexibly configured, and can be effectively integrated with robotic arms and automatic devices according to the layout and actual situation of the factory production line to form an efficient detection solution that meets the characteristics of different samples.

[Learn More](#)

Excitation Source	X-ray tube:Rhodium or tungsten anode target (optimized for application), 5 to 200 μ A, 8 to 50keV (4 W max)
Detector	High performance SDD detector
Power Supply	9 VAC power adapter
Analysis Mode	Alloy or Coating
Analysis range	Elements from Potassium(K19) to Uranium (U92)
IP Rating	IP54
Temperature Range	10C to 50C, continuous operation
Humidity	10 % to 90 % relative humidity, non-condensing
Operating System	Linux
Software	Proprietary data acquisition and processing software package

Benchtop Gold Analyzer

Item Number: XRF-200



Introduction

XRF 200 Benchtop Gold analyzer offers a rapid and remarkably precise method for assessing karat or gold content, serving quality control, pricing, and practical utilization needs.

[Learn More](#)

Excitation Source	X-ray tube:Rhodium or tungsten anode target (optimized for application), 5 to 200 μ A, 8 to 50keV (4 W max)
Detector	High performance SDD detector
Power Supply	9 VAC power adapter
Analysis Mode	Alloy or Coating
Analysis range	Elements from Potassium (K19) to Uranium (U92)
IP Rating	IP54
Temperature Range	10°C to 50°C, continuous operation
Humidity	10 % to 90 % relative humidity, non-condensing
Operating System	Linux
Software	Proprietary data acquisition and processing software package



Kintek Solution

Head Quarter: No.89 Science Avenue, High-Tech Zone,
Zhengzhou, China

