



KINTEK SOLUTION

Sieving Machine Catalog

Contact us for more catalogs of [Sample Preparation](#), [Thermal Equipment](#), [Lab Consumables & Materials](#), [Bio-Chem Equipment](#), etc.

KINTEK SOLUTION

COMPANY PROFILE

>>> About Us

Company Profile

Kintek Solution Ltd is one technology orientated organization, team members are devoted to probing the most efficient and reliable technology and innovations in the scientific researching equipment, fields like biochemical reacting, new materials researching, heat treatment, vacuum creating, refrigerating, as well as pharmaceutical and petroleum extracting equipment.

Products & Services

Kintek Solution Ltd is headquartered in Zhengzhou, the capital city of Henan Province, China, and its core business includes the manufacture, distribution and sale of all types of scientific research equipment and laboratory consumables. The wide range of products and services covers the following main areas:

- **Sample Preparation Equipment:** We provide high-performance sample preparation equipment such as tablet presses, ball mills, vibrating sieves and tablet punching machines, which are capable of meeting a wide range of sample preparation needs and ensuring high quality experimental data and research results.
- **Thermal Equipment:** Our thermal equipment includes tube furnaces, sintering furnaces, vacuum furnaces, atmosphere furnaces, graphite furnaces, dental furnaces, rotary furnaces, and high-temperature furnaces (e.g., MPCVD, CVD, PECVD, electric rotary kilns). These facilities excel in high-temperature processing and materials synthesis, meeting a wide range of needs from basic research to industrial production.
- **Biochemical equipment:** We offer a wide range of biochemical laboratory equipment, including rotary evaporators, vacuum pumps, cold trap chillers,

heating circulators, reactors, short-range distillation equipment, sterilization equipment, and homogenizers. These equipments are widely used in the fields of chemical reaction, biological processing and pharmaceutical manufacturing.

- **Laboratory Consumables:** We supply a wide range of laboratory consumables such as fine ceramic products, electrochemical consumables, PTFE material products, high purity materials, battery materials, chemical vapor deposition materials, optical materials, thin film deposition components and glass materials. These consumables provide the necessary support for laboratories to ensure the smooth running of experimental processes.

Technological Advantages

Kintek Solution Ltd has significant technological strengths in the field of scientific research equipment and technical solutions, which enable us to stand out in a competitive marketplace and support our customers with cutting-edge technology. The following are our key technological strengths:

Advanced R&D capabilities

- **Technological Innovation:** Our R&D team is committed to exploring and developing the latest technologies to keep our equipment at the forefront of the industry through continuous technological innovation.
- **Customized solutions:** Based on the specific needs of our customers, we are able to develop and provide customized equipment to meet specific research requirements and application scenarios.
- **Cooperative R&D:** We cooperate with leading research institutes and higher education institutions around the world to carry out R&D projects on cutting-edge technologies to ensure that our technologies are always at the forefront of the industry.

High-performance equipment

- **Precision design:** Our equipment adopts advanced design concepts to ensure high precision, reliability and performance to meet the stringent requirements of scientific research and industrial applications.
- **Advanced materials:** We use high-quality materials and components to improve the durability and stability of our equipment, extend its service life and reduce maintenance costs.

Strict quality control

- **Standardized production:** All equipment is manufactured in accordance with international quality standards, and each production step is strictly controlled to ensure product consistency and reliability.
- **Comprehensive testing:** Comprehensive performance testing and quality inspection are carried out before the equipment is delivered to ensure that it meets the customer's technical specifications and operational requirements.

Comprehensive technical support

- **Technical Service:** Provide comprehensive technical support and after-sales service, including equipment installation, commissioning, training and maintenance, to ensure that customers can use our products efficiently.
- **Rapid Response:** We have established a rapid response mechanism, which can promptly solve the problems encountered by customers in the process of use and reduce equipment downtime.

Innovative technology integration

- **System Integration:** We integrate advanced control systems and automation technologies into our equipment to improve operational efficiency and data accuracy, and streamline operational processes.

Through these technological advantages, Kintek Solution Ltd is able to continue to provide our customers with innovative, efficient and reliable scientific research equipment and solutions to promote the continuous progress of scientific research and industrial applications.

Market position and customers

Kintek Solution Ltd is positioned in the market as a leading global provider of high-tech research equipment and solutions, specializing in biochemical reactions, new materials research, heat treatment, vacuum manufacturing, refrigeration, as well as pharmaceuticals and oil extraction. We are committed to brand leadership in research equipment by providing innovative technology and high quality equipment to meet the needs of research organizations and industrial companies in complex research and production processes.

Core Market Positioning:

- **Specialization:** We focus on high technology and scientific research, providing advanced equipment and solutions for specialized research institutes, laboratories and industrial applications.
- **High-end customers:** Our main customers include world-renowned universities, research institutes and various industrial enterprises, which usually have high requirements for equipment performance and technology.
- **Technological Innovation:** We are committed to technological innovation and customized solutions to ensure that our customers receive cutting-edge technical support to meet the ever-changing needs and challenges in the market.

Market Customer Groups:

- **Research Institutes and Universities:** including the world's leading research institutes and institutions of higher learning, who require high-performance research equipment and technical support for basic research, applied research and technology development.
- **Industrial companies:** covering a wide range of industries such as pharmaceuticals, oil extraction, new materials manufacturing and electronic materials production, these companies rely on reliable equipment and solutions to ensure product quality and productivity during production.
- **Laboratories and test centers:** organizations that provide laboratory services and quality testing, requiring accurate laboratory equipment and instruments for sample analysis and testing.
- **Technology Development Companies:** Companies that specialize in the development and application of new technologies and have a high demand for innovative equipment and technical solutions to support their R&D projects and technology validation.

Through clear market positioning and customer groups, we are committed to promoting scientific and technological progress, supporting the innovation and development of our global customers, and continuing to provide high-quality products and services to the market.

Team Introduction

The team at Kintek Solution Ltd is at the heart of the company's success. In order to realize our vision and maintain our leadership position in the field of high-tech research equipment, we are committed to building an exceptional team with the following attributes:

1. Professionalism

- **Technical Expertise:** Our team consists of technical experts and engineers in the field with deep expertise and technical backgrounds to meet complex technical challenges and innovation needs.
- **Industry experience:** We bring together professionals with extensive experience in the fields of research equipment, material science and engineering technology to ensure a precise grasp of market needs and technological trends.

2. Innovative Spirit

- **R&D-driven:** The team encourages innovative thinking and technological exploration, supports employees to participate in R&D projects on cutting-edge technologies, and continuously pushes forward the technological advancement of products and solutions.
- **Flexible Adaptation:** In the face of changing market environment, we have the ability to adapt quickly and flexibly to meet the changing needs of our customers.

3. Collaboration and Communication

- **Cross-sectoral collaboration:** The team maintains close collaboration between various departments, including R&D, production, sales and customer service, to ensure the smooth progress of projects and timely response to customer needs.
- **Efficient Communication:** Emphasize internal communication and information sharing, through efficient communication mechanisms and tools to ensure that all team members are consistent with the project goals and progress.

4. Customer Orientation

- **Customer Service:** Team members are customer-focused and committed to providing quality service and support to ensure that our customers have the best experience in using our products and solutions.

- Customized solutions: the ability to deeply understand the specific needs of customers and provide customized solutions to meet the special requirements of different customers.

5. Professional Training and Development

- Continuous Learning: We provide continuous training and learning opportunities for our team members to ensure that they are always up-to-date with the latest technology and industry knowledge.
- Career Development: We value the career development and growth of our employees, provide clear career paths and promotion opportunities, and motivate our employees to realize their personal goals and career aspirations within the company.

6. Corporate Culture

- Integrity and Responsibility: The team upholds integrity and responsibility, treats work and customers with honesty and fairness, and builds trust and long-term cooperative relationships.
- Unity and Collaboration: Focusing on the spirit of teamwork, the team emphasizes mutual support and joint efforts to achieve the company's goals and promote the overall success of the team.

By building such a highly qualified, innovation-driven and customer-oriented team, we ensure that Kintek Solution Ltd continues to lead in the field of scientific research equipment and provide excellent products and services to our customers worldwide.

At KINTEK, technology fuels our corporate spirit. This dynamic energy awaits you upon joining our team. Expect a distinctive cultural environment where our global business focus opens doors to diverse customs and traditions worldwide. Here, challenging roles promise to propel your career to new heights.

Our exceptional corporate culture sparks innovation, fosters care, and drives continuous progress among individuals and teams. Our team embodies youthfulness, positivity, enthusiasm, and a bold attitude toward challenges. Passionate about our business, our employees ardently contribute to the company's growth.

We seek individuals brave enough to embrace challenges, harbor grand ambitions, and thirst for knowledge. If you're driven by dreams and passion, and aspire to start your

entrepreneurial journey, KINTEK is the platform to actualize your career plans. We don't just offer opportunities; we pave the way for your future.

Join us at KINTEK, where innovation meets opportunity. Let's create a future that's as promising as your aspirations.

Future Plans

Kintek Solution Ltd's future plans are aimed at further strengthening our leadership position in the research equipment sector and driving the company forward in terms of technological innovation, market expansion and customer service. The following are our key future directions:

1. Technology Innovation and R&D

- Cutting-edge technology development: Continue to invest resources in the research and development of cutting-edge technologies, such as artificial intelligence, the Internet of Things and nanotechnology, in order to promote equipment intelligence and automation.
- New Product Lines: Expand existing product lines and develop equipment to meet emerging market needs, especially in the areas of biochemistry, biomedicine and high-performance materials.
- Cooperative R&D: Strengthen cooperation with international research institutes and institutions of higher learning to carry out joint R&D projects to ensure that the technology remains at the global leading level.

2. Market Expansion

- Global Market Expansion: Further expand the global market, especially in emerging markets and developing regions, establish more sales and service networks, and enhance the brand's international influence.
- Industry application: Explore and expand the application fields in other industries, such as new energy, environmental protection technology and intelligent manufacturing, to open up new business growth points.

3. Customer Service Enhancement

- Enhancement of customer support: Establish a more complete customer support system, provide 24/7 technical support and maintenance services, and ensure

the efficient experience of customers in the use of equipment.

- Customized services: Provide more customized services and solutions according to customers' individual needs to enhance customer satisfaction and loyalty.

4. Sustainable Development

- Environmentally friendly technology: Develop and adopt environmentally friendly materials and processes to reduce the environmental impact during the production and use of equipment and promote sustainable development.
- Energy saving and consumption reduction: Optimize the energy efficiency of equipment, reduce energy consumption, improve resource utilization efficiency, and support the development of green technology.

5. Internal optimization

- Intelligent management: Implement intelligent management systems and data analysis tools to improve productivity and management and reduce operating costs.
- Employee Training: Enhance employee training and skills upgrading to build a high-quality team to meet changing market demands and technological challenges.

6. Innovation ecosystem

- Establishment of innovation platform: Create innovation platforms and laboratories to support employees and partners in technological innovation and product development.
- Industry Chain Cooperation: Deepen cooperation with the upstream and downstream of the industry chain, integrate resources, and promote the development and implementation of industry technical standards and market norms.

Through these future plans, Kintek Solution Ltd will continue to lead the forefront of science and technology, provide customers with more advanced and reliable products and services, and at the same time, promote the sustainable development of the enterprise and the progress of the industry.



Hydraulic Diaphragm Lab Filter Press

Item Number: KH-01



Introduction

11

[Learn More](#)

Size	150*150 to 630*630 mm
Cake thickness	10 to 30 mm
Filter Press Chamber volume capacity	0.1 to 300 L
Max. Filter pressure	10 bar
Max. Membrane Squeezing pressurer	12 bar
Max. Filter temprature	90 °C
Filter press plate type	chamber plate,CGR plate,membrane plate etc.
Filter Press Filter plate feeding type	Center feeding,corner feeding etc.
Filtrate discharge way	Open or Close type
Cake washing type	washable or non-washable type
Filter press Compressing type	Automatic hydraulic,hydraulic jack etc.
Filter press plate shifting type	Manual operation,Automatic plate shifted one by one etc.
Filter plate material	PP, FRPP
Membrane material	PP,Rubber
Filter Press Frame material	Carbon steel paint antiseptis, SS304/316 etc.
Filter Feed/Liquid tube material	PP, SS304/316 etc.
Motor brand of hydraulic pump	ABB
reducer brand of plate shifting	SEW
reducer brand of cloth washing	SEW
Filter press cloth material	PP,PE,,Nylon etc. filter press cloth included for different testing purpose
Filter press feed pump	different filter press feeding pump,such as Air diaphragm pump,small screw pump or other small capacity pump for feeding

Vibration Sieve

Item Number: KT-V400



Introduction

Efficiently process powders, granules, and small blocks with a high-frequency vibration sieve. Control vibration frequency, screen continuously or intermittently, and achieve accurate particle size determination, separation, and classification.

[Learn More](#)

Maximum load	25 kg
Maximum number of stages	9/13kg
Maximum sieve tower mass	56 kg
Amplitude	0.8-4 mm
Vibration frequency	3000 times/min
Screening particle size range	75 um-125 mm
The largest available screen diameter	400mm
Maximum sieve tower height	960mm
Additional function	Comfortable visual screen press plate
Screening method	Dry
Electrical description	100-120V/200-240V AC, 50-60Hz, 1500W
Power port	National standard / European standard / American standard / British standard, etc.
Net weight	98 kg
Dimensions (width, thickness and height)	600*660*1260mm
Protection level	IP65
Standard	CE/ISO9001

Dry Three-Dimensional Vibrating Sieve

Item Number: KT-V200



Introduction

The KT-V200 product focuses on solving common sieving tasks in the laboratory. It is suitable for sieving 20g-3kg dry samples.

[Learn More](#)

Maximum load	3 kg
Screen layers	1-8 floors
Maximum sieve tower mass	4 kg
Amplitude	0.2-3 mm
Vibration frequency	3000 times/min
Screening particle size range	20 um-125 mm
The largest available screen diameter	200mm
Maximum sieve tower height	510mm
Additional function	Comfortable visual screen press plate
Screening method	Dry
Electrical description	100-120V/220-240VAC,50-60Hz,200W
Power port	National standard/European standard/American standard/British standard, etc.
Net weight	35 kg
Dimensions (width, thickness and height)	300*405*685mm
Protection level	IP65
Standard	CE/ISO9001

Wet Three-Dimensional Vibrating Sieve

Item Number: KT-VM200



Introduction

The wet three-dimensional vibrating sieving instrument focuses on solving the sieving tasks of dry and wet samples in the laboratory. It is suitable for sieving 20g - 3kg dry, wet or liquid samples.

[Learn More](#)

Maximum load	3 kg
Screen layers	1-8 floors
Maximum sieve tower mass	4 kg
Amplitude	0.2-3 mm
Vibration frequency	3000 times/min
Screening particle size range	20 um-125 mm
The largest available screen diameter	200mm
Maximum sieve tower height	510mm
Additional function	Comfortable visual screen press plate
Screening method	Dry
Electrical description	100-120V/200-240V AC, 50-60Hz, 1500W
Power port	National standard / European standard / American standard / British standard, etc.
Net weight	37 kg
Dimensions (width, thickness and height)	300*405*730mm
Protection level	IP65
Standard	CE/ISO9001

Dry And Wet Three-Dimensional Vibrating Sieve

Item Number: KT-VD200



Introduction

KT-VD200 can be used for sieving tasks of dry and wet samples in the laboratory. The screening quality is 20g-3kg. The product is designed with a unique mechanical structure and an electromagnetic vibrating body with a vibration frequency of 3000 times per minute.

[Learn More](#)

Maximum load	3 kg
Screen layers	1-8 floors
Maximum sieve tower mass	4 kg
Amplitude	0.2-3 mm
Vibration frequency	3000 times/min
Screening particle size range	20 um-125 mm
The largest available screen diameter	200mm
Maximum sieve tower height	510mm
Additional function	Comfortable visual screen press plate
Screening method	dry wet
Electrical description	100-120V/200-240V AC, 50-60Hz, 1500W
Power port	National standard/European standard/American standard/British standard, etc.
Net weight	42 kg
Dimensions (width, thickness and height)	430*400*620mm
Protection level	IP65
Standard	CE/ISO9001

Two-Dimensional Vibrating Sieve

Item Number: KT-VT150

NEW



Introduction

KT-VT150 is a desktop sample processing instrument for both sieving and grinding. Grinding and sieving can be used both dry and wet. The vibration amplitude is 5mm and the vibration frequency is 3000-3600 times/min.

[Learn More](#)

Product name	Micro three-dimensional vibrating screener
Processing principle	High frequency three-dimensional parabolic motion
Application sample characteristics	Powder granular small pieces loose suspension, etc.
Processing type	Particle size determination, separation, classification
Maximum load	3kg
Number of screen layers	1-8 floors
Maximum sieve tower mass	2kg
Amplitude	0.2-3 mm
Vibration frequency	3000 times/minute
Screening particle size range	20um-125mm
Maximum screen diameter available	100mm
Maximum screen tower height	510mm
The main function	Timing Password lock Continuous screening One-key reset for intermittent screening Alarm sound Dry and wet screening Amplitude adjustment
Additional features	Comfortable visual screen pressure plate liquid circulation system
Screening method	Dry
Electrical description	100-120V/200-240V AC,50-60Hz,100W
Power port	National standard/European standard/American standard/British standard, etc.
Net weight	42kg
Dimensions (width, depth, height)	430*400*620mm
Protection level	IP65
Standard	CE/ISO9001

Slap Vibrating Sieve

Item Number: KT-T200TAP



Introduction

KT-T200TAP is a slapping and oscillating sieving instrument for laboratory desktop use, with 300 rpm horizontal circular motion and 300 vertical slapping motions to simulate manual sieving to help sample particles pass through better.

[Learn More](#)

Maximum number of stages	3 kg
Screen layers	1-8 floors
Maximum number of stages	7
Amplitude	5-10 mm
Vibration frequency	300 times/min
Screening particle size range	20 um-25 mm
The largest available screen diameter	200mm
Maximum sieve tower height	510mm
Additional function	Fully enclosed cabinet with sound insulation Quick locking device LED lighting
Screening method	dry wet
Electrical description	100-120V/200-240V AC, 50-60Hz, 180W
Power port	National standard/European standard/American standard/British standard, etc.
Net weight	85 kg
Dimensions (width, thickness and height)	410*470*715mm
Protection level	IP65
Standard	CE/ISO9001



Kintek Solution

Head Quarter: No.89 Science Avenue, High-Tech Zone,
Zhengzhou, China

