

10-50L Jacket Glass Reactor

Item Number: KR-10



Introduction

Discover the Versatile 10-50L Jacket Glass Reactor for Pharmaceutical, Chemical, and Biological Industries. Accurate Stirring Speed Control, Multiple Safety Protections, and Customizable Options Available. KinTek, Your Glass Reactor Partner.

[Learn More](#)

| Model | KGR-10 | KGR-20 | KGR-30 | KGR-50 |
|---------------------|--|-----------------|-----------------|----------------|
| Reactor Volume | 10L | 20L | 30L | 50L |
| Jacket Volume | 3L | 6L | 10L | 16L |
| Stirring Power | 60W | 90W | 180W | 180W |
| Max. Torque | 132N/cm | 200N/cm | 200N/cm | 273N/cm |
| Port Sealing | PTFE | | | |
| Speed Control | Knop Stepless Speed Regulation | | | |
| Stirring Speed | 0-650rpm | | | |
| Working temperature | -80~250°C | | | |
| Vacuum | 0.098Mpa | | | |
| Safety Protection | Over-current/ ground fault/over-temperature protection | | | |
| Working Environment | 5-35°C | | | |
| Power Supply | 110-440V, 50/60Hz | | | |
| Overall Dimensions | 600*580*2000 mm | 700*580*2100 mm | 640*600*2280 mm | 700*630*2500mm |
| Net weight | 75kg | 125kg | 135kg | 140kg |