

10-50L Jacketed Glass Reactor Vessel For Lab Applications

Item Number: KR-10



Introduction

Discover the Versatile 10-50L Jacket Glass Reactor for Pharmaceutical, Chemical, and Biological Industries. Accurate Stirring Speed Control, Multiple Safety Protections, and Customizable Options Available. KinTek, Your Glass Reactor Partner.

[Learn More](#)

Model	KGR-10	KGR-20	KGR-30	KGR-50
Reactor Volume	10L	20L	30L	50L
Jacket Volume	3L	6L	10L	16L
Stirring Power	60W	90W	180W	180W
Max. Torque	132N/cm	200N/cm	200N/cm	273N/cm
Port Sealing	PTFE			
Speed Control	Knop Stepless Speed Regulation			
Stirring Speed	0-650rpm			
Working temperature	-80~250°C			
Vacuum	0.098Mpa			
Safety Protection	Over-current/ ground fault/over-temperature protection			
Working Environment	5-35°C			
Power Supply	110-440V, 50/60Hz			
Overall Dimensions	600*580*2000 mm	700*580*2100 mm	640*600*2280 mm	700*630*2500mm
Net weight	75kg	125kg	135kg	140kg