

10-50L Single Jacketed Glass Reactor Vessel For Lab Applications

Item Number: KR-10S



Introduction

Looking for a reliable single glass reactor system for your lab? Our 10-50L reactor offers precise temperature and stirring control, durable support, and safety features for synthetic reactions, distillation, and more. KinTek's customizable options and tailored services are here to meet your needs.

[Learn More](#)

Model	KGR-10	KGR-20	KGR-30	KGR-50
Reactor Volume	10L	20L	30L	50L
Stirring Power	60W	90W	180W	180W
Max. Torque	132N/cm	200N/cm	200N/cm	273N/cm
Port Sealing	PTFE			
Speed Control	Knop Stepless Speed Regulation			
Stirring Speed	0-650rpm			
Working temperature	-80~250°C			
Vacuum	0.098Mpa			
Safety Protection	Over-current/ ground fault/over-temperature protection			
Working Environment	5-35°C			
Power Supply	110-440V, 50/60Hz			
Overall Dimensions	600*580*2000 mm	700*580*2100 mm	640*600*2280 mm	700*630*2500mm
Net weight	75kg	125kg	135kg	140kg