

10L Short Path Distillation

Item Number: SPD-10



Introduction

Extract and purify mixed liquids with ease using our 10L short path distillation system. High vacuum and low temperature heating for optimal results.

[Learn More](#)

Glassware	Glass material	High borosilicate glass 3.3
	Flask volume	10L
	Receiver flask	2*1000ml
	Cold trap	Dry ice type condensor
Heating mantle	Heating power	2100W
	Temperature range	RT-380°C
	Thermometer	PT100
	Stirring method	Magnetic
	Stirring power	40W
	Stirring speed	50-2000RPM
Chilling circulator	Temperature range	-10-99°C
	Reserver volume	10L/200*180*160mm
	Pump flowrate	6L/min
Vacuum pump	Pump type	Dual stage rotary vane pump
	Pumping rate	2.2L/S at 50HZ; 2.6L/S at 60HZ
	Ultimate pressure	3Pa
	Power rating	400/370kW
	Net weight	21kg
Fittings	Supportor	150*150mm SS jack with cork ring
	Vacuum piping	Silicon hose
	Keck clamp	SS/Plastic
	Thermometer	Range 0-200°C with 30cm length