

304 316 Stainless Steel Vacuum Ball Valve Stop Valve For High Vacuum Systems

Item Number: KT-VA11



Introduction

Discover 304/316 stainless steel vacuum ball valves, Ideal for high vacuum systems, Ensure precise control and durability. Explore now!

[Learn More](#)

Parameter	Specification
Product Type	Vacuum Ball Valve/Vacuum Stop Valve
Material	304/316 Stainless Steel
Working Pressure	10 ⁻⁸ mbar - 1000 mbar
Working Temperature	-196°C - 200°C
Leakage Rate	≤10 ⁻⁹ mbar-l/s
Operation Mode	Manual/Pneumatic/Electric
Connection Mode	Flange/Thread/Welding
Size	DN10 - DN100
Application	Semiconductor, Photovoltaic, Scientific Research