

Manual Button Battery Sealing Machine (Digital Display)

Item Number: PC2NS



Introduction

The manual button battery sealing machine is a small device specially used for button battery packaging. It is easy to operate and suitable for laboratories and small batch production to ensure that the battery is firmly sealed and improve production efficiency.

[Learn More](#)

Instrument model	PC2NS
Pressure range	0-2T (0-25MPa)
Piston diameter	32mm(d) in chrome-plated oil cylinder
Pressure gauge	Digital display 0.00-40.00MPa
Standard mold	Standard CR20 series package mold
Sealing mold	Optional CR16, CR20, CR24, CR30, etc.
Sealing pressure	Generally between 0.8-1.2 tons
Shell removal mold	Optional CR16, CR20, CR24, CR30, etc.
Shell removal pressure	Generally within 0.4 tons
Overall dimensions	210*165*290mm(LX*W*H)
Equipment weight	12Kg

Machine size diagram