

# Button Battery Case Gasket For Battery Lab Applications

Item Number: BC-02



## Introduction

The gasket prevents the deformation of the internal material, and the spring sheet is conducive to the tight contact inside the battery to prevent loosening.

[Learn More](#)

Model Specifications	Specifications (diameter*thickness)
CR20 gasket	φ15.8*0.5mm
	φ15.8*1.0mm
	φ15.8*1.5mm
	φ16.1*0.5mm
	φ16.1*0.8mm
CR24 gasket	φ16.2*1.5mm
	φ19.0*1.0mm
	φ20.0*0.4mm