

# Button Battery Tablet Press Sealing Mold For Lab Use

Item Number: PMN



## Introduction

The sealing die is essential for assembling button batteries, ensuring components like the anode, cathode, and electrolyte are securely enclosed.

[Learn More](#)

Instrument model	PMN
Dual-purpose mold	Sealing, opening and dual-use
Sealing function	CR16,CR20,CR24,CR30 optional
Sealing pressure	0.8-1.2 Ton
Dismantling function	CR16,CR20,CR24,CR30 optional
Dismantling pressure	
Diagram of hydraulic powder press size	