

# Button Battery Tablet Press Sealing Mold

Item Number: PMN



## Introduction

The sealing die is essential for assembling button batteries, ensuring components like the anode, cathode, and electrolyte are securely enclosed.

[Learn More](#)

|  |                               |
|--|-------------------------------|
| Instrument model                       | PMN                           |
| Dual-purpose mold                      | Sealing, opening and dual-use |
| Sealing function                       | CR16,CR20,CR24,CR30 optional  |
| Sealing pressure                       | 0.8-1.2 Ton                   |
| Dismantling function                   | CR16,CR20,CR24,CR30 optional  |
| Dismantling pressure                   |                               |
| Diagram of hydraulic powder press size |                               |