


Proton Exchange Membrane For Batteries Lab Applications

Item Number: BC-20



Introduction

Thin proton exchange membrane with low resistivity; high proton conductivity; low hydrogen permeation current density; long life; suitable for electrolyte separators in hydrogen fuel cells and electrochemical sensors.

[Learn More](#)

model	N-117 or N117	NafionN115	NR211	NRE-212
thickness:	183um	127Micron	25.4Micron	50.8Micron
Weight:	/	250g/m2	50g/m2	100g/m2
Specification:	10*10cm	40*40CM	61cm*L	/
Conductivity:	0.083S/cm	0.083S/cm	0.083S/cm	0.083S/cm
Exchange capacity:	0.89meq/g	0.89meq/g	0.95-1.01	0.95-1.01 meq/g