

Engineering Advanced Fine Alumina (Al₂O₃) Ceramic Positioning Pin Straight Bevel For Precision Applications

Item Number: KM-C012



Introduction

Alumina ceramic positioning pin has the characteristics of high hardness, wear resistance and high temperature resistance.

[Learn More](#)

model	small head diameter	middle diameter	Bevel Diameter	length
M4	3.1mm	4.8mm	9.7mm	22mm
M5	4mm	5.5mm	9.6mm	22mm
M6	4.7mm	6.7mm	9.5mm	26mm
M8	6.3mm	8.5mm	12mm	26mm
M9	6.3mm	9.7mm	12.9mm	28.9mm
M10	8.3mm	10.7mm	13.6mm	24.5mm
M12	9.5mm	12.7mm	14.8mm	26.5mm
M13	10mm	13.7mm	16.8mm	32.9mm

model	small head diameter	middle diameter	Bevel Diameter	length
M4	3mm	4.7mm	7.7mm	24.3mm
M5	4mm	5.5mm	9.6mm	22mm
M6	4.8mm	6.7mm	9.9mm	26mm
M8	6.2mm	8.8mm	11.9mm	25.7mm
M10	8.3mm	10.6mm	14.2mm	26.7mm
M12	9.1mm	12.6mm	14.7mm	30.5mm
M14	12.5mm	14.8mm	15.7mm	28.7mm