

# Cf/Kf Flange Vacuum Electrode Feedthrough Lead Sealing Assembly For Vacuum Systems

Item Number: KT-VA08



## Introduction

Discover high-vacuum CF/KF flange electrode feedthroughs, ideal for vacuum systems. Superior sealing, excellent conductivity, and customizable options.

[Learn More](#)

Parameter Description	Options / Specifications
Flange specifications	CF16, CF25, CF40, CF63, CF100, KF16, KF25, KF40, KF50, KF63 (customizable)
Lead length	100mm, 200mm, 300mm, 500mm, 1000mm (customizable)
Maximum operating temperature	400°C (customizable)
Maximum operating pressure	$10^{-8}$ Pa
Sealing material	Ceramic, metal