

Dental Porcelain Zirconia Sintering Ceramic Furnace Chairside With Transformer

Item Number: KT-DS10



Introduction

Experience top-notch sintering with Chairside Sintering Furnace with Transformer. Easy to operate, noise-free pallet, and automatic temperature calibration. Order now!

[Learn More](#)

Heating speed	200°C/min max. (392°F /minute)
Max temperature	1530°C
Max temperature holding time	2 hours
Electric power supply	100-120V 50/60HZ 230V 50/60HZ
Rated current	14.5ampere@110V 7.0ampere@230V
Rated output power	max 1500w
Dimension	H27cm x W36cm x D56cm
Firing chamber diameter	9cm(3.5")
Net weight	20Kg
Weight with package	25.5Kg