

# Customer Made Versatile Cvd Tube Furnace Cvd Machine

Item Number: KT-CTF16



## Introduction

Get your exclusive CVD furnace with KT-CTF16 Customer Made Versatile Furnace. Customizable sliding, rotating, and tilting functions for precise reactions. Order now!

[Learn More](#)

Furnace model	KT-CTF16-60
Max. temperature	1600°C
Constant work temperature	1550°C
Furnace tube material	High purity Al2O3 tube
Furnace tube diameter	60mm
Heating zone	3x300mm
Chamber material	Alumina polycrystalline fiber
Heating element	Silicon Carbide
Heating rate	0-10°C/min
Thermal couple	S type
Temperature controller	Digital PID controller/Touch screen PID controller
Temperature control accuracy	±1°C
Gas precise control unit	
Flow meter	MFC mass flow meter
Gas channels	3 channels
Flow rate	MFC1: 0-5SCCM O2 MFC2: 0-20SCMCH4 MFC3: 0- 100SCCM H2 MFC4: 0-500 SCCM N2
Linearity	±0.5% F.S.
Repeatability	±0.2% F.S.
Pipe line and valve	Stainless steel
Maximum Operating Pressure	0.45MPa
Flow meter controller	Digital Knob controller/Touch screen controller
Standard vacuum unit(Optional)	
Vacuum pump	Rotary vane vacuum pump
Pump flow rate	4L/S
Vacuum suction port	KF25

Vacuum gauge	Pirani/Resistance silicon vacuum gauge
Rated vacuum pressure	10Pa
High vacuum unit(Optional)	
Vacuum pump	Rotary vane pump+Molecular pump
Pump flow rate	4L/S+110L/S
Vacuum suction port	KF25
Vacuum gauge	Compound vacuum gauge
Rated vacuum pressure	6x10-5Pa

Above specifications and setups can be customized

No.	Description	Quantity
1	Furnace	1
2	Quartz tube	1
3	Vacuum flange	2
4	Tube thermal block	2
5	Tube thermal block hook	1
6	Heat resistant glove	1
7	Precise gas control	1
8	Vacuum unit	1
9	Operation manual	1