

# Diaphragm Vacuum Pump

Item Number: LE301



## Introduction

Get stable and efficient negative pressure with our Diaphragm Vacuum Pump. Perfect for evaporation, distillation, and more. Low temperature motor, chemical resistant materials, and environmentally friendly. Try it today!

[Learn More](#)

power	parameter
Motor power (W)	180
Power supply	220-240V~, 50Hz
Suction diameter (mm)	∅10×∅6
Maximum vacuum (MPa) /	0.0992/8
Ultimate pressure (mbar)	
Maximum pumping rate (L/min)	25
Dimensions (mm)	310W×225D×168H
Weight (Kg)	10
Operating ambient temperature (°C)	5~35
Ambient relative humidity (%)	≤ 70
Enclosure protection class	IP20
Anti-pollution	level 2

Inlet and outlet nozzle connection hose specifications: (outer diameter × inner diameter) (mm) Rubber hose: ∅12×∅6