

Double-Layer Water Bath Electrolytic Electrochemical Cell

Item Number: ELCWD



Introduction

Discover the temperature-controllable electrolytic cell with a double-layer water bath, corrosion resistance, and customization options. Complete specifications included.

[Learn More](#)

Specification	50ml ~ 250ml
Applicable temperature range	0 ~ 60°C
Sealed form	Thread + Apron
Material	Boron glass + PTFE
Electrolytic cell hole	Three electrode holes (6mm), two air holes (3mm), custom openings are available
Specification	50ml ~ 500ml
Applicable temperature range	0 ~ 60°C
Material	Boron glass + PTFE
Electrolytic cell hole	Three electrode holes (6mm), custom openings are available