


Electric Button Battery Sealing Machine

Item Number: PP2N



Introduction

The electric button battery sealing machine is a high-performance packaging equipment designed for mass production of button batteries (such as CR series, LR series, SR series, etc.), suitable for electronic manufacturing, new energy research and development, and industrial automation production lines.

[Learn More](#)

Instrument model	PP2N
Pressure range	50-1500kg
Pressure-adding process	Program pressurization - program pressure maintenance - timed pressure release
Pressure-holding time	0-999 seconds
Pressure conversion	Program automatically converts the pressure that the mold can withstand
LCD display	4.3-inch LCD screen
Sealing mold	Optional CR16, CR20, CR24, CR30, etc.
Shell removal mold	Optional CR16, CR20, CR24, CR30, etc.
Standard mold	Standard CR20 series packaging mold
Dimensions	220*240*380(L*W*H)
Equipment power supply	220V(50Hz/60Hz)
Equipment weight	35kg
Machine size diagram	