

Filter Testing Machine(Fpv)

Item Number: RPM-06



Introduction

This machine is suitable for testing the dispersion properties of polymers such as pigments, additives and masterbatches by extrusion and filtration.

[Learn More](#)

| Model No. | RPM-06A | RPM-06B |
|--------------------------------|---|----------------------------|
| Control system | Computer Control | |
| Screw diameter | 20/25/30mm (or customized) | |
| Main motor power | 4KW (or customized) | |
| length to diameter ratio (L/D) | 28:1 | |
| Rpm Screw speed | 0-95rpm Frequency conversion speed regulation | |
| Pressure sensor | 0-35Mpa | |
| Filter | According to EN13900-5:2005 standard | According to ASTM standard |
| Outside dimension mm(W*D*H) | 1553*650*1350mm | 1553*650*1350mm |
| Weight (kg) | About 350kg | About 300kg |
| Power Supply | 3φ AC380V | |