

H Type Electrolytic Cell Triple Electrochemical Cell

Item Number: ELCH



Introduction

Experience versatile electrochemical performance with our H-type Electrolytic Cell. Choose from membrane or non-membrane sealing, 2-3 hybrid configurations. Learn more now.

[Learn More](#)

Specification	30ml~ 500ml
Applicable temperature range	0 ~ 60°C
Applicable membrane area	15mm (can be customized)
Material	Boron glass + PTFE
Electrolytic cell punching	Three electrode holes (6mm) Four gas (3mm) can be customized opening

Specification	30ml~ 500ml
Applicable temperature range	0 ~ 60°C
Applicable membrane area	0.5cm ² /1cm ²
Material	Boron glass + PTFE
Electrolytic cell punching	Three electrode holes (6mm) Six air holes (3mm) can be customized