

High Energy Planetary Ball Mill Milling Machine For Laboratory

Item Number: KT-P4000



Introduction

The biggest feature is that the high energy planetary ball mill can not only perform fast and effective grinding, but also has good crushing ability

[Learn More](#)

Grinding principle	Impact & friction force
Suitable materials	Small and medium-low hardness; brittle; dry or wet
Materials input size	
Materials output size	0.1-20 um
Processing volume	4000ml
Disc panspeed	800 r/min
Grinding panmaterial	Tungsten carbide;Ceramic; Agate; Stainless steel; Harden steel; Nylon, etc.
Planetary disk space movement mode	X axis planetary movement
Motor power	100-120V/200-240V AC ,50-60Hz,750W
Net weight	106kg
Dimensions	L720*W500*H500 mm
Protection level	IP65
Quality standards	CE