

Laboratory Horizontal Planetary Ball Mill Milling Machine

Item Number: KT-P400H



Introduction

Improve sample uniformity with our Horizontal Planetary Ball Mills. KT-P400H reduces sample deposition and KT-P400E has multi-directional capabilities. Safe, convenient and efficient with overload protection.

[Learn More](#)

Grinding principle	Impact & friction force
Suitable materials	Small and medium-low hardness; brittle; dry or wet
Materials input size	
Materials output size	0.1-20 um
Processing volume	
Grinding jar speed	0-900 r/min
Grinding jar material	Tungsten carbide; Ceramic; Agate; Stainless steel; Harden steel; Nylon, etc.
Number of grinding jar	4 pcs
Grinding jar volume	100 ml
Grinding ball material	Tungsten carbide; Zirconia; Alumina; Agate; Stainless steel, etc.
Motor power	250W
Net weight	35 kg
Dimensions	L320 * W410 * H510 mm
Protection level	IP65
Quality standards	CE