

Alumina (Al₂O₃) Ceramic Rod-Insulated

Item Number: KM-C09



Introduction

Insulated alumina rod is a fine ceramic material. Alumina rods have excellent electrical insulating properties, high chemical resistance and low thermal expansion.

[Learn More](#)

| | | | | | | | | |
|-----------|-----------|------------|----------|----------|----------|----------|----------|----------|
| 0.4*100mm | 0.9*100mm | 3.2*100mm | 6*100mm | 13*114mm | 18*86mm | 40*100mm | 8*300mm | 24*400mm |
| 0.5*100mm | 1*100mm | 3.5*100mm | 7*100mm | 14*114mm | 18*100mm | 50*100mm | 10*300mm | 30*400mm |
| 0.6*100mm | 2*100mm | 4*100mm | 8*100mm | 15*100mm | 20*100mm | 60*100mm | 12*300mm | |
| 0.8*100mm | 2*150mm | 4.5*90mm | 9*100mm | 16*100mm | 25*100mm | 4*300mm | 15*300mm | |
| 0.7*100mm | 2.5*100mm | 4.75*100mm | 10*100mm | 15*100mm | 30*100mm | 5*300mm | 16*300mm | |
| 0.8*100mm | 3*100mm | 5*100mm | 12*100mm | 16*100mm | 35*100mm | 6*300mm | 20*300mm | |