

# Custom Ptfе Teflon Parts Manufacturer For Ito Fto Glass And Silicon Wafer Storage Turnover Racks

Item Number: PTFE-18



## Introduction

ITO/FTO glass storage rack/turnover rack/silicon wafer storage rack can be used for the shipment packaging, turnover and storage of silicon wafers, chips, germanium wafers, glass wafers, sapphire wafers, quartz glass and other materials.

[Learn More](#)

Model	4 inches 25 pieces	4 inches 50 pieces	5 inches 25 pieces	5 inches 50 pieces	6 inches 25 pieces	8 inches 25 pieces	12 inches 25 pieces
Outer diameter	122mm	122mm	149mm	149mm	180mm	245mm	350mm
Excluding sponge inner diameter	110mm	110mm	138mm	138mm	*	*	320mm
Sponge inner diameter	104mm	104mm	127mm	127mm	*	*	300mm
height	29mm	56mm	45mm	55mm	43mm	40mm	60mm

Instructions This product is a flat silicon wafer box that can store 25 or 50 pieces of products with a diameter of 100mm, 125mm, 150mm, 200mm, and 300mm. It can be used for the shipment packaging, turnover, and storage of silicon wafers, chips, germanium wafers, glass wafers, sapphire wafers, quartz glass and other materials.

Model	2 inches 25 pieces	3 inches 25 pieces	4 inches 25 pieces	6 inches 25 pieces
External size	160*62*62mm	160*88*88mm	165*145*122mm	180*142*185mm
Capacity	Can be equipped with 25 pieces with a diameter of 50mm	Can be equipped with 25 pieces with a diameter of 76mm	Can be equipped with 25 pieces with a diameter of 100mm	Can be equipped with 25 pieces with a diameter of 150mm
Material	PP	PP	PP	PP
Color	Translucent	Translucent	Translucent	Translucent
weight	155g	240g	400g	600g