

Kf Ultra-High Vacuum Observation Window 304 Stainless Steel Flange High Borosilicate Glass Sight Glass

Item Number: KT-VA04



Introduction

Discover KF Ultra-High Vacuum Observation Window: 304 Stainless Steel Flange & High Borosilicate Glass Sight Glass, Ideal for precise observation in ultra-high vacuum environments.

[Learn More](#)

Model	Outer diameter	Inner diameter (view diameter)	Maximum temperature	Thickness	Material
KF 25	40mm	23mm	350°C	15.5mm	304 stainless steel + Borosilicate
KF 40	55mm	20mm		15.5mm	
KF 50	75mm	34mm		16mm	