

Kf Ultra-High Vacuum Observation Window Stainless Steel Flange Sapphire Glass Sight Glass

Item Number: KT-VA03



Introduction

Discover the KF Ultra-High Vacuum Observation Window, featuring sapphire glass and stainless steel flange for clear, reliable observation in ultra-high vacuum environments. Ideal for semiconductor, vacuum coating, and scientific research applications

[Learn More](#)

Model	Outer diameter	Inner diameter (view diameter)	Maximum temperature	Thickness	Material
KF 25	40mm	23mm	350°C	15.5mm	304 stainless steel + sapphire glass
KF 40	55mm	23mm		15.5mm	
KF 50	75mm	34mm		16mm	