

Kf/Iso Stainless Steel Vacuum Flange Blind Plate For High Vacuum Systems

Item Number: KT-VA12



Introduction

Discover KF/ISO stainless steel vacuum flange blind plates, ideal for high vacuum systems in semiconductor, photovoltaic, and research labs. High-quality materials, efficient sealing, and easy installation.

[Learn More](#)

Specifications	A	B	C	D
ISO63	95mm	12mm	70mm	90mm
ISO80	110mm	12mm	83mm	105mm
ISO100	130mm	12mm	102mm	125mm
ISO125	155mm	12mm	127mm	150mm
ISO160	180mm	12mm	153mm	175mm
ISO200	240mm	12mm	213mm	235mm
ISO250	290mm	12mm	261mm	285mm
ISO320	370mm	17mm	318mm	365mm
ISO400	450mm	17mm	400mm	445mm
ISO500	550mm	17mm	501mm	545mm
ISO630	690mm	22mm	651mm	685mm

Specifications	A	B
KF10	12.2mm	30mm
KF16	17.2mm	30mm
KF25	26.2mm	40mm
KF40	41.2mm	55mm
KF50	52.2mm	75mm
KF63	70mm	87mm
KF80	83mm	114mm
KF100	102mm	134mm
KF160	153mm	190mm

Specifications	A	B	C*no	P.C.D
CF16	34mm	7.5mm	4.4*6	26.9mm

CF25	54mm	10.5mm	6.6*6	43mm
CF35	70mm	12.7mm	6.7*6	58.7mm
CF50	86mm	16mm	8.4*8	72.4mm
CF63	114mm	18mm	8.4*8	92.1mm
CF80	130mm	18mm	8.4*16	110mm
CF100	152mm	20mm	8.4*16	130.3mm
CF150	202mm	22mm	8.4*20	181mm
CF200	253mm	24.5mm	8.4*24	231.8mm
CF250	305mm	26mm	8.4*32	284mm
CF300	368mm	28.5mm	10.8*36	338.1mm
CF350	419.1mm	28.5mm	10.8*36	388.9mm