

Lab Internal Rubber Mixer Rubber Kneader Machine For Mixing And Kneading

Item Number: RPM-07



Introduction

Lab internal rubber mixer is suitable for mixing, kneading and dispersing various chemical raw materials such as plastics, rubber, synthetic rubber, hot melt adhesive and various low-viscosity materials.

[Learn More](#)

Model No.	RPM-07A	RPM-07B	RPM-07C	RPM-07D
Mixing volume	1L	3L	5L	10L
Control Mode	Key Control/PLC Control (Optional)			
Discharge method	Reverse discharge or open close type			
Drive motor	3.75KW	7.5KW	11KW	18.5KW
Flip motor	0.75KW	0.75KW	0.75KW	0.75KW
Rotor speed (front/rear)	40/31r min(adjustable)			
Flip angle	110°			
Air pressure	0.5-0.8Mpa			
Volume (H*W*D)	1800*900*1900mm	1900*1300*1500mm	1900*1300*1500mm	2100*1100*2300mm
Weight (kg)	850kg	1300kg	1500kg	1800kg
Power Supply	3φAC380V			
*Special models can be designed according to customers 'requirements.				