

Casting Machine

Item Number: RPM-02

Introduction

The cast film machine is designed for the molding of polymer cast film products and has multiple processing functions such as casting, extrusion, stretching, and compounding.

[Learn More](#)

Model No.	RPM-02A	RPM-02B
Name	Single layer	3 layers
Screw diameter	25mm(or customized)	
L/D[Ratio of length to diameter]	33:1(or customized)	
Screw speed	0-95rpm(Frequency conversion speed regulation)	
Motor power	4KW(or customized)	
Die lip width	300mm(or customized)	
Optional configuration	3CC melt pump or customized[Manual or hydraulic screen changer][Pressure sensor][Pressure sensor][Unwinding device	
calendering part	160x350mmx2or customized	
Installation method of calender roller	Vertical or parallel	
Winding device	Friction winding	
(WxDxH) Volume	2800x800x1650mm	3500x1600x2200mm
Weight(kg)	≈ 750kg	≈ 1.2T
Power Supply	3φ[AC380V	