

# Laboratory Sealed Hammer Crusher For Efficient Sample Preparation

Item Number: KT-PCZ



## Introduction

Discover the Laboratory Sealed Hammer Crusher for efficient sample preparation. Ideal for coal, metallurgy, and research, this crusher ensures high production efficiency and environmental friendliness.

[Learn More](#)

Model	Feeding Size (mm)	Discharging Size (mm)	Productivity (kg/h)	Motor Power (kw)
PCZ-180x150	≤50	<6, <3, <1 (adjustable)	<600	1.5
PCZ-250x360	≤150	<13, <6, <3 (adjustable)	<1200	3
PCX-180x150	≤50	<3 (adjustable)	<120	1.5