

# Laboratory Oscillating Orbital Shaker

Item Number: KTL-5



## Introduction

Mixer-OT orbital shaker uses brushless motor, which can run for a long time. It is suitable for vibration tasks of culture dishes, flasks and beakers.

[Learn More](#)

Model	Mixer-OS 2s
Voltage	AC100-240V/DC24V
Frequency	50-60Hz
Display mode	LCD screen
Motor output power	40W
Oscillation mode	Track
Maximum load	7.5kg
Motor output power	40W
Speed range	30-250rpm
Motor type	Brushless motor
Timing range	1min-24h or permanent
Net weight	13kg
Dimensions	360×420×100mm