

# Molybdenum Tungsten Tantalum Evaporation Boat For High Temperature Applications

Item Number: KME01



## Introduction

Evaporation boat sources are used in thermal evaporation systems and are suitable for depositing various metals, alloys and materials. Evaporation boat sources are available in different thicknesses of tungsten, tantalum and molybdenum to ensure compatibility with a variety of power sources. As a container, it is used for vacuum evaporation of materials. They can be used for thin film deposition of various materials, or designed to be compatible with techniques such as electron beam fabrication.

[Learn More](#)

Length 100 width 8 thickness 0.2/0.3mm

Length 100 width 15 thickness 0.2/0.3/0.5mm

Length 100 width 20 thickness 0.2/0.3/0.5mm

Groove size: length 50 deep 2.6