

Multi Heating Zones Cvd Tube Furnace Machine Chemical Vapor Deposition Chamber System Equipment

Item Number: KT-CTF14



Introduction

KT-CTF14 Multi Heating Zones CVD Furnace - Precise Temperature Control and Gas Flow for Advanced Applications. Max temp up to 1200°C, 4 channels MFC mass flow meter, and 7" TFT touch screen controller.

[Learn More](#)

Furnace model	KT-CTF14-60
Max. temperature	1400°C
Constant work temperature	1300°C
Furnace tube material	High purity Al ₂ O ₃ tube
Furnace tube diameter	60mm
Heating zone	2x450mm
Chamber material	Alumina polycrystalline fiber
Heating element	Silicon Carbide
Heating rate	0-10°C/min
Thermal couple	S type
Temperature controller	Digital PID controller/Touch screen PID controller
Temperature control accuracy	±1°C
Gas precise control unit	
Flow meter	MFC mass flow meter
Gas channels	4 channels
Flow rate	MFC1: 0-5SCCM O ₂ MFC2: 0-20SCMCH ₄ MFC3: 0- 100SCCM H ₂ MFC4: 0-500 SCCM N ₂
Linearity	±0.5% F.S.
Repeatability	±0.2% F.S.
Pipe line and valve	Stainless steel
Maximum Operating Pressure	0.45MPa
Flow meter controller	Digital Knob controller/Touch screen controller
Standard vacuum unit(Optional)	
Vacuum pump	Rotary vane vacuum pump
Pump flow rate	4L/S

Vacuum suction port	KF25
Vacuum gauge	Pirani/Resistance silicon vacuum gauge
Rated vacuum pressure	10Pa
High vacuum unit(Optional)	
Vacuum pump	Rotary vane pump+Molecular pump
Pump flow rate	4L/S+110L/S
Vacuum suction port	KF25
Vacuum gauge	Compound vacuum gauge
Rated vacuum pressure	6x10 ⁻⁵ Pa

Above specifications and setups can be customized

No.	Description	Quantity
1	Furnace	1
2	Quartz tube	1
3	Vacuum flange	2
4	Tube thermal block	2
5	Tube thermal block hook	1
6	Heat resistant glove	1
7	Precise gas control	1
8	Vacuum unit	1
9	Operation manual	1