

# Optical Water Bath Electrolytic Electrochemical Cell

Item Number: ELCWO



## Introduction

Upgrade your electrolytic experiments with our Optical Water Bath. With controllable temperature and excellent corrosion resistance, it's customizable for your specific needs. Discover our complete specifications today.

[Learn More](#)

Specifications	50ml ~ 250ml
Applicable temperature range	0 ~ 60°C
Sealing form	Thread + Apron
Material	boron glass + PTFE
Electrolytic cell opening	three electrode holes (6mm), two air holes (3mm), can be customized
Specifications	50ml ~ 250ml
Applicable temperature range	0 ~ 60°C
Material	boron glass + PTFE
Electrolytic cell opening	three electrode holes (6mm), can be customized