

Rubber Vulcanizer Vulcanizing Machine Plate Vulcanizing Press For Lab

Item Number: RPM-01



Introduction

The Plate vulcanizing press is a kind of equipment used in the production of rubber products, mainly used for the vulcanization of rubber products. Vulcanization is a key step in rubber processing.

[Learn More](#)

| Model No. | RPM-01A | RPM-01B | RPM-01C | RPM-01D |
|------------------------|--|-----------------|---------------------------------|-----------------|
| Control Mode | Manual | Electric | PLC control | Vacuum |
| Capacity | 30/50/100ton or customized | | | |
| Temperature range | Room temperature~300°C | | | |
| Size of working plates | 300*300mm or customized | | | |
| Work layer | Single layer heating or integrated cooling and heating | | | |
| Cooling mode | Water cooling | | water cooling or linear cooling | |
| (W*D*H) Volume | 540*400*1250mm | 1100*600*1580mm | 1100*600*1580mm | 1500*600*1580mm |
| Weight (kg) | 210kg | 780kg | 780kg | 900kg |
| Power supply | 3φAC380V | | | |