

Powerful Plastic Crusher Machine

Item Number: KT-HX



Introduction

KINTEK's powerful plastic crusher machines process 60-1350 KG/H of diverse plastics, ideal for labs and recycling. Durable, efficient, and customizable.

[Learn More](#)

Model	180	250	300	400	500	600	700	800
Crushing capacity KG/H	60-110	160-210	215-320	270-480	420-730	470-820	580-950	670-1350
Voltage V	220/380V	380V						
Motor power KW	2.2	4	5.5	7.5	11	15	22	30
Motor power HP	3	5	7.5	10	15	20	30	40
Rotation diameter MM	195	220	220	220	250	275	310	380
Number of blades	6+2	9+2	9+2	12+2	15+2	18+4	21+4	24+4
Number of claw blades	None	12+2	15+2	18+2	21+2	27+4	None	None
Number of flat blades	None	3+2	3+2	3+2	6+2	6+4	6+4	6+4
Screen aperture MM	6	8	8	8	10	10	12	12
Feed port size MM	180×180	260×180	310×220	420×250	510×280	610×310	720×420	820×470
Overall dimensions CM	75×55×95	95×63×102	105×68×120	114×80×128	140×102×152	150×114×160	155×124×185	185×140×202
Machine weight KG	125	230	320	440	580	750	1000	1450