

Precision Machined Zirconia Ceramic Ball For Engineering Advanced Fine Ceramics

Item Number: KM-G03



Introduction

zirconia ceramic ball have the characteristics of high strength, high hardness, PPM wear level, high fracture toughness, good wear resistance, and high specific gravity.

[Learn More](#)

1mm	2.778mm	4.763mm	6.747mm	9.0mm	12.7mm	16.668mm	25.0mm	40mm
1.2mm	3.0mm	5.0mm	7.0mm	9.525mm	13.494mm	17.4625mm	25.4mm	50mm
1.5mm	3.175mm	5.556mm	7.144mm	10.0mm	14mm	18.256mm	28mm	
1.588mm	3.5mm	5.953mm	7.938mm	10.318mm	14.288mm	19.05mm	28.575mm	
2.0mm	3.969mm	6.0mm	8.0mm	11.1125mm	15.0mm	20.0mm	30.0mm	
2.381mm	4.0mm	6.35mm	8.5mm	11.509mm	15.875mm	20.638mm	35mm	
2.5mm	4.5mm	6.5mm	8.731mm	12.0mm	16.0mm	22.225mm	38.1mm	