

Ptfe Electrolytic Cell Electrochemical Cell Corrosion-Resistant Sealed And Non-Sealed

Item Number: ELCP



Introduction

Choose our PTFE Electrolytic Cell for reliable, corrosion-resistant performance. Customize specifications with optional sealing. Explore now.

[Learn More](#)

Specification	10ml ~ 1000ml
Applicable temperature range	0 ~ 60°C
Sealed form	thread + apron
Material	PTFE
Electrolytic cell punching	Three electrode holes (6mm), two air holes (3mm), custom openings are available
Specification	10ml ~ 1000ml
Applicable temperature range	0 ~ 60°C
Material	PTFE
Electrolytic cell punching	Three electrode holes (6mm), custom openings are available