

# Button Battery Disassembly And Sealing Mold For Lab Use

Item Number: PCKM



## Introduction

The simple sealing and disassembly mold can be directly used on ordinary tablet presses, which can save costs, is convenient and fast, and can be used to encapsulate and disassemble button batteries. Other specifications can be customized.

[Learn More](#)

Instrument model	Button battery removal mold	Button battery sealing mold
Disassembly die	CR16,CR20,CR24,CR30 optional	CR16,CR20,CR24,CR30 optional
Disassembly pressure		0.8-1.2Ton
Dimensions	Φ60*140mm(L*H)	Φ60X140mm(LXH)
Weight	1.85kg	1.85kg

Sealing mold size diagram