

Side Window Optical Electrolytic Electrochemical Cell

Item Number: ELCOS



Introduction

Experience reliable and efficient electrochemical experiments with a side window optical electrolytic cell. Boasting corrosion resistance and complete specifications, this cell is customizable and built to last.

[Learn More](#)

Specifications	50ml ~ 1000ml
Applicable temperature range	0 ~ 60°C
Sealing form	thread
Material	glass + PTFE
Opening hole of electrolytic cell	Three electrode holes (6mm), two air holes (3mm), custom openings are available
Specifications	50ml ~ 1000ml
Applicable temperature range	0 ~ 60°C
Sealing form	thread
Material	PTFE
Opening hole of electrolytic cell	Three electrode holes (6mm), two air holes (3mm), custom openings are available