

Small Injection Molding Machine

Item Number: RPM-09



Introduction

The servo system has fast and stable movements; good controllability and repeatability, super energy saving; the product can be automatically dropped and formed; the machine body is low, convenient for feeding, easy to maintain, and no height restrictions on the installation site.

[Learn More](#)

Model No.	RPM-09
Control Mode	PID control or PLC program control
Calendering rollers	2-4 (or customized)
Diameter of roller	120mm□160mm□200mm(or customized)
Installation method of calender roller	Vertical or parallel
Range of film thickness	0.1mm~5mm (or customized)
Roller speed	0-30r/min(adjustable)
Motor power	4kw(or customized)
Unwinding device	Friction roll
Winding device	Friction winding
Volume (W*D*H)	1300*950*1600mm
Weight(kg)	About 900kg About 900kgs
Power Supply	3φ□AC380V