

Stainless Steel Laboratory Ball Mill For Dry Powder And Liquid With Ceramic Polyurethane Lining

Item Number: KT-M



Introduction

Discover the versatile stainless steel dry powder/liquid horizontal ball mill with ceramic/polyurethane lining. Ideal for ceramic, chemical, metallurgical, and building materials industries. High grinding efficiency and uniform particle size.

[Learn More](#)

Specification	KT-M200	KT-M300	KT-M500	KT-M1000	KT-M1500	KT-M2000
Grinding drum speed	50	50	45	35	32	30
Motor power(kw)	4	4	5.5	11	15	30
Grinding drum capacity	200L	300L	500L	1000L	1500L	2000L
Loading volume	90L	135L	220L	450L	700L	900L