

# Tungsten Evaporation Boat For Thin Film Deposition

Item Number: LMF-TEB



## Introduction

Learn about tungsten boats, also known as evaporated or coated tungsten boats. With a high tungsten content of 99.95%, these boats are ideal for high-temperature environments and widely used in various industries. Discover their properties and applications here.

[Learn More](#)

Models	Thickness (mm)	Width (mm)	Length (mm)	Shape
#207	0.2	7	100	
#215	0.2	15	100	
#308	0.3	8	100	
#310	0.3	10	100	Round bottom / Flat bottom / Butterfly / Customizable
#315	0.3	15	100	
#413	0.4	13	50	
#525	0.5	25	78	