

Rubber Processing Machine Water Cooled Strips Series

Item Number: RPM-03



Introduction

Our rubber processing machine is designed for the mixing and processing experiments of engineering plastics, modified plastics, waste plastics and masterbatches.

[Learn More](#)

Model No.	RPM-03A	RPM-03B
Control system	PLC control	PLC control
Capacity (kg)	About 1-10kg/h(decide by formula)	About 30kg/h(decide by formula)
Feeder	Twin screw quantitative feeding or customized	
Screw diameter	21.7mm(or customized)	35mm(or customized)
L:D(Length to diameter ratio)	40 : 1	40:1-48:1
rpm Screw speed	0-300rpm	0-500rpm
Motor	4KW	18.5KW
Cooling device	Air/water cooling (optional)	
Cutting device	Water strips/underwater cutting/hot cutting	
Screen changer	Manual screen changer	
Power	12KW	25KW
Volume (mm)(W*D*H)	4000*550*1600mm	6800*960*1940mm
Weight (kg)	About 580kg	About 1900kg
Power Supply	3φ, AC380V	