

# Ultra-Vacuum Electrode Feedthrough Connector Flange Power Electrode Lead For High-Precision Applications

Item Number: KT-VA09



## Introduction

Discover the Ultra-Vacuum Electrode Feedthrough Connector Flange, perfect for high-precision applications. Ensure reliable connections in ultra-vacuum environments with advanced sealing and conductive technology.

[Learn More](#)

| Parameter Description         | Options  |
|-------------------------------|--|
| Flange specifications         | CF16, CF25, CF40, CF63, CF100, KF16, KF25, KF40, KF50, KF63 (customizable) |
| Lead length                   | 100mm, 200mm, 300mm, 500mm, 1000mm (customizable)                          |
| Maximum operating temperature | 400°C (customizable)   |
| Maximum operating pressure    | 10 <sup>-10</sup> Pa   |
| Sealing material              | Ceramic, metal   |