

Uv Lamp Trolley For Laboratory And Hospital Use

Item Number: KT-P05



Introduction

The UV lamp trolley is made of cold-rolled plate sprayed with plastic, and adopts a double-lamp structure; it is movable, foldable, and equipped with universal wheels, which is very convenient to use.

[Learn More](#)

Model	KT-C-I	KT-B-I	KT-C-II	KT-B-II
Voltage	AC220V 50Hz			
Input power	70VA		130VA	
Number of tubes	2x30W		4x30W	
Timing range	0-120min			
UV wavelength	253.7nm			
Irradiation intensity	≥90μ w/cm ²			
Lamp arm adjustment angle	90°□120°□150°			
Outer packing size (mm)	1160x410x370			
Weight	18kg		24kg	