

Vacuum Arc Furnace Induction Melting Furnace

Item Number: KT-VA



Introduction

Discover the power of Vacuum Arc Furnace for melting active & refractory metals. High-speed, remarkable degassing effect, and free of contamination. Learn more now!

[Learn More](#)

Model	KT-VA1	KT-VA5	KT-VA25	KT-VA200
Capacity (Kg)	1	5-15	25	200
Working voltage (V)	20-40			
Working current (A)	1000A	3000A	6000A	12000A
Vacuum pressure (Pa)	1.3-1.3x10 ⁻²			
Electrode size (mm)	Φ25-40 x 400	Φ10-45x1200	Φ30-60x1350	Φ56-150x1745
Ingot size (mm)	Φ60x100	Φ80x135	Φ100x400mm	Φ200x670mm
Dimensions (m)	0.8x0.35x1.8	3.81x3.0x5.21	4.43x3.33x4.93	7.4x3.4x6.72