

Vacuum Dental Porcelain Sintering Furnace

Item Number: KT-DV10



Introduction

Get precise and reliable results with KinTek's Vacuum Porcelain Furnace. Suitable for all porcelain powders, it features hyperbolic ceramic furnace function, voice prompt, and automatic temperature calibration.

[Learn More](#)

Heating speed	200°C/min max. (392°F /minute)
Max temperature	1200°C max(2283°F)
Max temperature holding time	2 hours
Vacuum level	1-101%
Electric power supply	100-120V 50/60HZ 230V 50/60HZ
Rated current	14.5ampere@110V 7.0ampere@230V
Rated output power	max 1500w
Dimension	H27cm x W36cm x D53cm
Firing chamber diameter	9cm(3.5")
Net weight	20Kg
Weight with package	23.5Kg