

Wall Mounted Water Distillation Unit

Item Number: KT-C01



Introduction

The wall mounted water distillation unit can be installed on the wall and is designed to produce high-quality distilled water continuously, automatically and efficiently at low economic cost.

[Learn More](#)

| | |
|-------------------|------------------------|
| Model | KT-3.5~4.5L/h |
| Power supply | AC220V~240V/50Hz -60Hz |
| Water output | 3.5-4.5L/h |
| Power | 1.5Kw x2 |
| Net weight | 7kg/set |
| Gross weight | 8kg/set |
| Box size | 740x400x140mm/set |
| Evaporator volume | 5.5liter |
| PH value | 5-6 |